

ChemScan mini LowCrVI Analyzer

The ChemScan LowCrVI analyzer provides operators with reliable process chemistry measurements. This reduces the need for frequent manual sampling or laboratory analysis while producing the best water quality.

APPLICATIONS

• Analysis of Hexavalent Chromium in potable water, wastewater and industrial processes

FEATURES

- Robust design for demanding operating environments
- Blockage-resistant internal sample tubing
- No filtration required on samples with low solids
- Minimal replacement parts for low maintenance
- Sample Blank eliminates electrical/optical drift
- Simple field adjustable calibration
- Separate enclosures for electronic and sample handling
- LED light source for 10+ years design life
- Self-Cleaning to eliminate internal fouling
- Separate external sample line cleaning available
- Full range of sampling accessories available for all applications

BENEFITS

- Assure process conformance
- Control energy and chemical costs
- Confirm plant compliance in real time
- Improve process performance
- Low reagent and maintenance costs

ACCESSORIES



Sample Extraction Accessory

Provides a continuous flow of fresh sample to the ChemScan mini analyzer. Designed to reject algae and other larger solids.



ChemScan Cartridge Filter Wand

For high-solids applications. No pressurized air, water or chemicals required for cleaning.

ChemScan mini Outdoor Enclosure

A turnkey solution for mounting the ChemScan analyzer and related items.



Submersible Pump Provides a continuous flow of fresh sample to sample extraction accessory.



Deck-Mounted Self-Priming Pump

Provides a continuous flow of fresh sample to sample-extraction accessory. (when submersible pump is not applicable)

Discuss with your ChemScan representative the most suitable accessories for your application.

in-situ.com



Mini LowCrVI Technical Specifications¹

FUNCTIONS AND OUTPUTS

ANALYZER OPERATION	Automated, Continuous Analysis of Water and Wastewater
MEASUREMENT PRINCIPLE	Reagent-Assisted Optical Absorbance with sample zero correction
NUMBER OF PARAMETERS	One
PARAMETER OPTION	Hexavalent Chromium
DATA COMMUNICATIONS	4-20 mA(2 outputs)
DATA LOG	Time Date, Date, Concentration, Diagnostic Info, 5,000 events
NUMBER OF SAMPLE LINES	One
REAGENT ADDITION	YES, Direct Reagent Injection
AUTO MAINTENANCE	Auto Clean
CALIBRATION	Factory calibrated for reagent response, field adjustable
SAMPLE PARAMETERS	
SAMPLE PRESSURE	Pressurized sample line required regulated to 2-10 psi (15-70 kPa), (sample conditioning and pressurizing accessories available)
SAMPLE FLOW	0.5 to 1.0 l/min. 1 L Flush Per Sample (0.13 to 0.26 GPM $$ - 0.26 Gallon Flush)
FILTRATION REQUIREMENT	For samples with more than 150 mgl TSS (filter required for WW influent and primary effluent)
STRAINER REQUIREMENT	#20 Mesh - Opening of 0.7 mm (0.027 inches) Provided
SAMPLE TEMPERATURE	50-140°F (10° - 60°C)
SAMPLE TURBIDITY	60NTU or 150mg/l Suspended Solids
OPERATING ENVIRONMENT	
ENCLOSURE RATINGS	Upper Enclosure: NEMA 4X Fiberglass Reinforced Polyester, Acrylic window Lower Enclosure NEMA 4X Fiberglass Reinforced Polyester
AMBIENT TEMPERATURE	41 - 113°F (5° - 45°C)
RELATIVE HUMIDITY	0 - 100% (Non-Condensing)
INSTALLATION	Indoor or Sheltered (from rain and sun) Location

PERFORMANCE SPECIFICATIONS ²		
READING INTERVAL	12 to 5999 minutes	
DEFAULT READ INTERVAL	17 minutes	
RESPONSE TIME	12 minutes minimum	
ACCURACY	2% of value or 2x detection limit (whichever is greater) Per EPA SP 846 (The detection limit is the low concentration stated in ranges below)	
PRECISION	Less than 0.5% of Range	
ZERO DRIFT	Less than 0.5% of Range	
RANGES	Method 1040 0.03 - 5.0 mg/L	
INSTRUMENT SPECIFICATIONS		
SIZE	26" tall x 9.5" wide x 7" deep (66 cm tall x 24 cm wide x 18 cm deep)	
WEIGHT	27 lbs (12.25 kg)	
FINISH COATING MATERIAL	Fiberglass Reinforced Polyester (FRP)	
POWER	120-240 VAC ±10%, 50-60 Hz, 70 VA	
POWER CONNECTION	120 VAC US cord / plug set (Standard) (conduit connection optional)	
POWER CONDITION	Dedicated branch circuit free from: surges/dips > 10%, RF and switching noise	
OPERATOR INTERFACE	2 x 20 LCD and 4 x 4 Keypad	
SAMPLE CONNECTION	¼" FNPT Fitting	
WASTE CONNECTION	6 foot length of 5/8" ID clear vinyl tube provided (route to open drain)	
MOUNTING	Wall (Standard)	
MAINTENANCE		
REAGENT REPLACEMENT	As required (3 months at default read interval)	
CLEANING SOLUTIONS REFILL	As required (3 months typical)	
PERISTALTIC MIXING PUMP HEAD	Replace after six months of operation	
PERISTALTIC MIXING PUMP FULL ASSEMBLY	Replace after twelve months of operation	
PERISTALTIC ZEROING/ CLEANING PUMP HEAD	Replace after two years of operation	



Notes:
Technical Specifications are subject to change without prior notice.
All performance specifications are based on analysis of drinking water standards under factory conditions

in-situ.com



in Online Monitoring for Environment

Thị phần số 1 Việt Nam về

GIẢI PHÁP QUAN TRẮC MÔI TRƯỜNG & ĐO LƯỜNG CÔNG NGHIỆP



Trụ sở chính

Số 4E, đường số 6, phường An Phú , Thành Phố Thủ Đức, Thành Phố Hồ Chí Minh. Hotline: (+84) 901 379 116



Việt An Miền Bắc

Lô 33, khu BT4-1, dự án khu nhà ở Trung Văn, phường Trung Văn, quận Nam Từ Liêm, Hà Nội Hotline: (+84) 901 851 116

Việt An Miền Trung

Số 5A Mai Xuân Thưởng, phường Hòa Khê, quận Thanh Khê, Thành Phố Đà Nẵng Hotline: (+84) 898 119 116



Eurowater Technology

Số 9A, đường số 6, phường An Phú, TP. Thủ Đức, TP. Hồ Chí Minh. Hotline: (+84) 909 788 959

Văn phòng Hà Tĩnh

Tổ dân phố Liên Phú, phường Kỳ Liên, thị xã Kỳ Anh, Hà Tĩnh Hotline: (+84) 938 442 414

www.vietan-group.com | www.vietan-enviro.com